

Product Safety Information

Safety cabinet type 30 asecos Q-CLASSIC-30, hinged doors, W 1164 x D 620 x H 1947 mm

Manufacturer/Responsible Person: asecos GmbH, Weiherfeldsiedlung 16-18, 63584 Gründau, Deutschland

E-Mail: info@asecos.com

Please note the technical data of the products!

Article Numbers: 462138, 462137, 462136, 462135, 462134, 462133, 462132

Safety Instructions:

- The safety storage cabinet is fire-retardant (F30): Keep it away from open flames or extreme temperatures.
- Wear suitable personal protective equipment when storing and handling toxic and flammable substances.
- Protection against explosive vapours: Connect to the technical exhaust air system and ensure proper functioning of the ventilation.
- Always keep hinged doors closed to minimise security risks and unauthorised access. Use the profile cylinder lock correctly.
- The maximum load capacity of the shelves is 75 kg. Do not overload to prevent structural failure.
- Carry out regular maintenance and inspection of the oven and the ventilation system to ensure safety and functionality.
- Consult safety data sheets to avoid uncertainties when handling chemical substances.
- Use only by qualified personnel and operate the appliance in accordance with the relevant operating instructions.
- Only use suitable, GHS-categorised (1-4) substances for safe storage.
- The floor drip tray has a volume of 33 litres. Take immediate action to contain any overflows.
- Use security locks to protect materials from unauthorised access.
- Provide emergency plans and equipment for handling chemicals.